ANT95R

Single-Axis Rotary Direct-Drive Nanopositioning Stages

High resolution (0.01 arc sec) High performance Unlimited rotation Outstanding error motion specifications Excellent in-position stability Multi-axis configurations High dynamic performance



Introduction

The ANT95R direct-drive rotary stages are designed as part of Aerotech's nano Motion Technology product family. Our rotary stages offer unprecedented in-position stability (0.005 arc sec) and sub 0.01 arc-sec incremental motion performance, and are offered in two grades of accuracy.

Multi-Axis Capabilities


The ANT95R series is designed for compatibility and easy integration with Aerotech's ANT linear stage product offerings. Together these stages provide accuracy, stability, and small-size performance capability for almost any nano-manufacturing or inspection application.

Dynamic Performance

In addition to the high precision levels, these systems offer high dynamic performance and throughput ideal for processes that require speed and precision.

Durability

The ANT95R stage series was designed to operate in a 24/7 manufacturing environment. Unlike other rotary devices, the ANT95R requires no periodic maintenance, assuring years of trouble-free operation.



Replaceable O-ring seals are available to support wet cutting of 0.5 mm to 5.8 mm tubing.

ANT95R Series SPECIFICATIONS

Mechanical Specifications		ANT95R-020	ANT95R-180	ANT95R-360	
Rotation Angle		20°	180°	±360° Continuous	
Accuracy ⁽¹⁾	BASE	10 arc sec	10 arc sec	10 arc sec	
	PLUS	3 arc sec	3 arc sec	3 arc sec	
Resolution (Minimum Incremental Motion)		0.01 arc sec	0.01 arc sec	0.01 arc sec	
Repeatability (Bi-Directional) ⁽¹⁾		1.5 arc sec	1.5 arc sec	1.5 arc sec	
Repeatability (Uni-Directional)		0.5 arc sec	0.5 arc sec	0.5 arc sec	
Tilt Error	Synchronous	NA	NA	10 arc sec	
Motion	Asynchronous	NA	NA	3 arc sec	
Axial	Synchronous	NA	NA	2 µm	
Error Motion	Asynchronous	NA	NA	0.5 µm	
Radial	Synchronous	NA	NA	3 µm	
Error Motion	Asynchronous	NA	NA	1 µm	
Maximum Speed		20 rpm	20 rpm	200 rpm	
Maximum Acceleration		400 rad/s ²	400 rad/s ²	400 rad/s ²	
In-Position Stability ⁽²⁾		0.005 arc sec	0.005 arc sec	0.005 arc sec	
Aperture		11 mm (0.433 in)	11 mm (0.433 in)	11 mm (0.433 in)	
Maximum Torque (Continuous)		0.2 Nm	0.2 Nm	0.2 Nm	
	Axial	2.0 kg (4.4 lb)	2.0 kg (4.4 lb)	2.0 kg (4.4 lb)	
Load Capacity ⁽³⁾	Radial	1.5 kg (3.3 lb)	1.5 kg (3.3 lb)	1.5 kg (3.3 lb)	
Capacity	Moment	2 Nm	2 Nm	2 Nm	
Rotor Inertia (Unloaded)		0.00065 kg-m ²	0.00066 kg-m ²	0.00069 kg-m ²	
Stage Mass		1.2 kg (2.6 lb)	1.2 kg (2.6 lb)	1.2 kg (2.6 lb)	
Material		Aluminum Body/Black Hardcoat Finish			
MTBF (Mean Time Between Failure)		30,000 Hours			


Notes: 1. Certified with each stage. Requires the use of an Aerotech controller. 2. In-Position Jitter listing is 3 sigma value. 3. Axis orientation for on-axis loading is listed. • Specifications are per axis, measured 25 mm above the tabletop. Consult factory for multi-axis or non-standard applications. • All error motion specifications are measured at 60 rpm. • For high speed operation, customer payload must be balanced to G1.0 per ISO 1940.


Electrical Specifications	ANT95R
Drive System	Slotless, Brushless, Direct-Drive Rotary Motor
Feedback	Noncontact Rotary Encoder
Maximum Bus Voltage	±40 VDC
Limit Switches	5 V, Normally Closed
Home Switch	Near Center

www.aerotech.com


NANO Technology ANT95R Series


ANT95R Series PERFORMANCE






ANT95R axial error plot illustrating outstanding synchronous and asynchronous error motion performance.





ANT95R Series DIMENSIONS



ANT95R Series ORDERING INFORMATION

Travel (Required)

-360	Continuous travel
-20	Limited travel, ± 10 degrees
-180	Limited travel, ±90 degrees

Mounting Plate (Optional)		
-MP	Mounting plate	
Performance Grade (Rec	red)	
-PL1	Base performance	
-PL2	High-accuracy performance, PLUS	

Integration (Required)

Aerotech offers both standard and custom integration services to help you get your system fully operational as quickly as possible. The following standard integration options are available for this system. Please consult Aerotech if you are unsure what level of integration is required, or if you desire custom integration support with your system.

-TAS	Integration - Test as system Testing, integration, and documentation of a group of components as a complete system that will be used together (ex: drive, controller, and stage). This includes parameter file generation, system tuning, and documentation of the system configuration.
-TAC	Integration - Test as components Testing and integration of individual items as discrete components that ship together. This is typically used for spare parts, replacement parts, or items that will not be used together. These components may or may not be part of a larger system.